



MOUNTING PLATE FOR CORNER EXTENSION

Material : 2,00 mm Galvanized steel

Supply includes : 2 pcs extension parts and assembly parts.

ENCLOSURE HEIGHT(H)	REFERENCE NO.
1200	712.121
1600	712.161
1800	712.181
2000	712.201
2200	712.221



SHORT MOUNTING PLATE APPLICATION

- ▼ Depth rails allow for use of shorter mounting plates inside the enclosure. Thereby, this allows for busbar support and busbar applications on the mounting plate.
- ▼ Each mounting plate needs 2 pcs depth rails and 4 pcs brackets. Please see page 75-77 for related products.
- ▼ Please see page 160-180 for busbar support needs.

! Attention : There is no inconvenience in using intermediate mounting plates and corner extension parts for short mounting plate applications. It can move front to back with these accessories



MOUNTING PLATE LEANING SYSTEM

- ▼ Used for placing the mounting plate in the backmost position inside the enclosure.

Material : 2.00 mm mild steel + zinc coated

Supply includes : 2 pcs mounting plate bracket and assembly parts

Reference number : **943.465** (2 pcs)

! Attention : Intermediate mounting plate and corner extension parts cannot be used in the mounting plate leaning application. Short mounting plate can be applied.

! Required : 6 pcs bracket required.



BAYING KIT

Material : 3,00mm - 4,00mm mild steel parts + zinc coated

Supply includes : 2 pcs combination, 4 pcs angular brackets,
2 pcs adjustable bracket, 4 pcs fixing bracket,
5,60m intermediate insulation gasket and mounting parts

Reference number : **711.000**

 **Note** : Please see page 105-107 for other combination and support systems.

